



Ordering codes – Elastomer couplings




Note:

In case of different inner diameters of the clamping hubs, the respective larger one is to be defined as output D 2

Ordering codes – Elastomer couplings ELT



Ordering codes – Intermediate spacer



For information purposes only – not required when placing orders!
Please contact WITTENSTEIN alpha for deviating mounting positions.

Ordering codes – Metal bellows couplings

[illegible]

Note:


In case of different inner diameters of the clamping hubs, the respective larger one is to be defined as output D 2

Ordering codes – Metal bellows couplings BCT


Product type	Size	Overall length	Coupling version	Inner diameter output D2	Output shape D2	Pitch circle drive D1	Gearbox model
BCT	00015 00060 00150 00300 01500 04000 06000 10000	Optional length A	A = standard B = including self opening clamp system (BCT-MF) S = Stainless steel, welded bellows	012,00 see technical data sheets	0 = Smooth 1 = Keyway (DIN 6885-A) 2 = Tooth hub (DIN 5480) 3 = Keyway (ANSI B17.1) 6 = 2 x Keyway (DIN 6885-A) (180°)	031,50 050,00 063,00 080,00 125,00 145,00 166,00	A = Flange pattern MA F = Flange pattern MF

For information purposes only – not required when placing orders!
Please contact WITTENSTEIN alpha for deviating mounting positions.

Ordering codes – Torque limiters



Ordering codes – Torque limiters TL1



For information purposes only – not required when placing orders!
Please contact WITTENSTEIN alpha for deviating mounting positions.