

motion control

All Electric Actuation Systems for Extreme Environments

0110

0

01010

Reliability Competence Sustainability

Component Range



Power and Control Electronics

- Product range from 12 V up to 900 V
- Up to 1,000 A output current
- Ambient temperatues from -46° C up to 75° C
- · SiiS-level-2 interface
- Designed and manufactured by WITTENSTEIN
- TRL7 since 2001



Planetary Gearboxes

- Product range up to 40,000 Nm
- Gear ratios from i=3 up to i=2,700
- Ambient temperatures from -46° C up to 75°C
- Designed and manufactured by WITTENSTEIN
- TRL7 since 2001

SSEAC[®] Subsea Proven Enabling All-Electric

- · Subsea electric actuator
- · Single channel or dual channel
- Double barrier sealing concept (optional)
- · API class 4 interface
- Up to 2,700 Nm torque
- · Qualified to 3,000 m water depth
- · 24 VDC to 400 V AC/DC variants
- MTBF > 100,000 h
- · Extensive condition monitoring
- · TRL4 up to TRL7



Brushless Motors

- Product range from 50 W up to 200 kW
- Ambient temperatures from -46° C up to 210° C
- Pressure resistant up to 1,800 bar
- Proven oil / hydraulic fluid compatibility
- · Pressure compensated operation in oil
- · Permanent excited by high grade magnets
- Designed and manufactured by WITTENSTEIN
- TRL7 since 2001



motion control

Contact:

WITTENSTEIN motion control GmbH Walter-Wittenstein-Straße 1 97999 Igersheim Deutschland

Tel.: +49 7931 493-0 E-Mail: info@wittenstein-motion-control.de

WITTENSTEIN – one with the future www.wittenstein-motion-control.de