


# TPM+ 订购代码



## 电机/齿轮箱组合表

速比	规格 004		规格 010			规格 025			规格 050			规格 110		
	DYNAMIC	POWER	DYNAMIC	POWER	HIGH TORQUE	DYNAMIC	POWER	HIGH TORQUE	DYNAMIC	POWER	HIGH TORQUE	DYNAMIC	POWER	HIGH TORQUE
4	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
5	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
7	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
10	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
16	53B	64B	64B	94C	x	94C	130D	x	130D	155D	x	130E	220D	x
20	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
21	53B	x	64B	x	x	94C	x	x	130D	x	x	130E	x	x
22	x	x	x	x	94C	x	x	130D	x	x	155D	x	x	220H
25	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
27,5	x	x	x	x	94C	x	x	130D	x	x	155D	x	x	220H
28	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
31	53B	x	64B	x	x	94C	x	x	130D	x	x	130E	x	x
35	x	64B	x	94C	x	x	130D	x	x	155D	x	x	220D	x
38,5	x	x	x	x	94C	x	x	130D	x	x	155D	x	x	220H
40	x	64A	x	94A	x	x	130A	x	x	155A	x	x	220B	x
50	x	64A	x	94A	x	x	130A	x	x	155A	x	x	220B	x
55	x	x	x	x	94C	x	x	130D	x	x	155D	x	x	220H
61	53A	x	64A	x	x	94A	x	x	130A	x	x	130D	x	x
64	53A	x	64A	x	x	94A	x	x	130A	x	x	130D	x	x
66	x	x	x	x	x	x	x	94C	x	x	130D	x	x	220D
70	x	64A	x	94A	x	x	130A	x	x	155A	x	x	220B	x
88	x	x	x	x	94C	x	x	94C	x	x	130D	x	x	220D
91	53A	x	64A	x	x	94A	x	x	130A	x	x	130D	x	x
100	x	64A	x	94A	x	x	130A	x	x	155A	x	x	220B	x
110	x	x	x	x	94C	x	x	94C	x	x	130D	x	x	155D
154	x	x	x	x	94A	x	x	94C	x	x	130D	x	x	155D
220	x	x	x	x	94A	x	x	94C	x	x	130D	x	x	155D

x = 非标准组合